



INSTALLATION PROCEDURE TERAX CABINET



JUNE 2010

THIS PRODUCT IS INTENDED FOR INDOOR USE ONLY.

The TERAX Cabinet Series has a weight limit of 100 pounds. Weight must be distributed equally throughout the cabinet. Cabinet must be installed in accordance with National Electric Code, and State and Local Regulations.

CAUTION: INSTALLER MUST USE APPROPRIATE HARDWARE (not supplied) AND A SUITABLE MOUNTING SURFACE ABLE TO SUPPORT 100 POUNDS IN ADDITION TO THE TERAX CABINET WEIGHT (stated above).

1. 1/4" hardware fasteners must be used to mount the TERAX Cabinet. Consult all applicable local building codes and regulations to determine proper mounting requirements. A Certified Professional Engineer is strongly recommended to verify installation.
2. Mark out locations where 1/4" hardware fasteners are to be placed.
3. Insert two 1/4" hardware fasteners in top of cabinet mounting holes (see figure, below) and hang TERAX Cabinet using a leveling instrument. When level, tighten down hardware fasteners. Once TERAX Cabinet is level and hardware fasteners are secure, install remaining two 1/4" hardware fasteners in bottom of cabinet mounting holes (see figure, below).



5290 Concourse Drive • Roanoke, VA 24019 USA
Phone: 540-265-0690 • TOLL FREE 800-622-7711
Fax: 540-265-0724 • www.occfiber.com